



Product: [83317E](#)

Electronic, 2 C #26 Str SPC, TFE Ins, OA SPC Brd, TFE Tape Jkt, MIL-W-16878/4 (Type E)

[Request Sample](#)

Product Description

High Temperature Electronic, 2 Conductor 26AWG (7x34) Silver Plated Copper, TFE Insulation, Overall Silver Plated Copper Braid(85%) Shield, TFE Tape Outer Jacket, MIL-W-16878/4 (Type E)

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
26	7x34	SPC - Silver Plated Copper	2

Conductor Count:	2
Total Number of Pairs:	1

Insulation

Material	Material Trade Name	Nominal Wall Thickness
TFE - Tetrafluoroethylene	Teflon®	0.01 in

Color Chart

Number	Color
1	White
2	Black

Outer Shield Material

Type	Material	Coverage [%]
Braid	SPC - Silver Plated Copper	85 %

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
TFE - Tetrafluoroethylene	Teflon®	0.121 in	0.011 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
39 Ohm/1000ft	7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
20.8 pF/ft	35.5 pF/ft

Inductance

Nominal Inductance
0.14 µH/ft

Current

Max. Recommended Current [A]
3 Amps per conductor @ 25°C

Voltage

UL Voltage Rating

600 V RMS

Temperature Range

Operating Temp Range: -65°C To +200°C

Mechanical Characteristics

Bulk Cable Weight: 12 lbs/1000ft

Max Recommended Pulling Tension: 26.8 lbs

Min Bend Radius/Minor Axis: 1.25 in

Standards

CPR Euroclass: Eca

Military Specification: MIL-W-16878/4 (Type E insulated conductors)

Other Specification: NEMA HP3

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU: Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2005-01-01

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability: IEC 60332-1-2

UL voltage rating: 600 V RMS

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item #	Color	UPC	Length	Footnote
83317E 009100	White	612825203926	100 ft	E
83317E 0091000	White	612825347514	1,000 ft	E
83317E 009500	White	612825203933	500 ft	E

Footnote: E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.

Product Notes

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

History

Update and Revision: Revision Number: 0.299 Revision Date: 12-19-2019

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

