


Product: [8416](#) 



Audio & Instrumentation, 2 Conductor 25 AWG TC, Individually Shielded, CM

Product Description

Dual Channel, 25 AWG stranded (7x33) Tinned Copper/Tinned Copper Covered Steel conductor, polyethylene insulation, individual TC spiral wrapped shield (90% coverage), PVC jacket, polarity rib on red conductor.

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	7x33	TC/TCCS -Tinned Copper/Tinned Copper Covered Steel	0.021 in	2

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.058 in

Color Chart

Number	Color
1	Red
2	Natural

Inner Shield Material

Type	Material	Coverage [%]
Spiral Serve	TC - Tinned Copper	90 %

Outer Shield Material

Type	Material	Coverage [%]
Serve	TC - Tinned Copper	90 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.106 x 0.213 in

Electrical Characteristics

Capacitance

Nom. Capacitance Conductor to Shield
36 pF/ft

Impedance

Nominal Characteristic Impedance
44 Ohm

Voltage

Non-UL Voltage Rating

90 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft
--------------------	---------------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length
8416 008250	Gray	612825355298	250 ft

History

Update and Revision:	Revision Number: 0.263 Revision Date: 08-22-2019
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.