


DRAWING NUMBER:	15-302-X-XX
PRODUCT GROUP:	TERMINALS
SUB-GROUP:	MILITARY NON-INSULATED TERMINALS
DESCRIPTION:	NON-INSULATED THRU-HOLE TURRET TERMINAL



BOARD / PANEL MOUNTING METHOD	MOUNTING HOLE SIZE	DRILL SIZE	FEED THRU COMBINATION
SWAGE MOUNT	0.067" ± 0.001	#51	N/A

PART NO. STRUCTURE:

15-302	-	X	-	XX
PART SERIES		DIMENSION		FINISH

MATERIAL OPTIONS:

15-302-X-XX

COMPONENT	MATERIAL	MATERIAL AND SPECIFICATION
TERMINAL	BRASS	BRASS PER ASTM B16, ALLOY C36000, 1/2 HARD

DIMENSION OPTIONS:

15-302-X-XX

DIMENSION	K	OVERALL LENGTH	SHANK LENGTH (L)	BOARD/PANEL THICKNESS
2	N/A	0.240"	0.084"	1/16"
3	N/A	0.271"	0.115"	3/32"
4	N/A	0.303"	0.147"	1/8"

FINISH - PLATING OPTIONS:

15-302-X-**XX**

FINISH CODE	COMPONENT	FINISH	FINISH AND SPECIFICATION
05	TERMINAL	ELECTRO-SOLDER	0.000300"MIN. ELECTRO-SOLDER PER SAE-AMS-P-81728 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418
088	TERMINAL	BRIGHT TIN-LEAD	0.000300"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418
095	TERMINAL	HOT SOLDER DIP	0.000100"MIN. HOT SOLDER DIP USING Sn60 PER IPC-J-STD-006 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418

TOLERANCES:*

DECIMAL	FRACTIONAL	ANGULAR	DRAWING ORIGATION DATE	LAST MODIFICATION DATE
± 0.005	N/A	± 3°	10/28/2002	3/1/2017

*All dimensions are in inches.

RoHS COMPLIANCE:

15-302-2-XX

PART NUMBER	RoHS COMPLIANT
15-302-2-05	NO
15-302-2-088	NO
15-302-2-095	NO

15-302-3-XX

PART NUMBER	RoHS COMPLIANT
15-302-3-05	NO
15-302-3-088	NO
15-302-3-095	NO

15-302-4-XX

PART NUMBER	RoHS COMPLIANT
15-302-4-05	NO
15-302-4-088	NO
15-302-4-095	NO

MILITARY REFERENCE SPECIFICATIONS:

15-302-2-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-302-2-05	MIL-T-55155/16	M55155/16XH01	A-A-59126/16	AA59126/16XH01
15-302-2-088	MIL-T-55155/16	M55155/16XJ01	A-A-59126/16	AA59126/16XJ01
15-302-2-095	MIL-T-55155/16	M55155/16XI01	A-A-59126/16	AA59126/16XI01

15-302-3-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-302-3-05	MIL-T-55155/16	M55155/16XH02	A-A-59126/16	AA59126/16XH02
15-302-3-088	MIL-T-55155/16	M55155/16XJ02	A-A-59126/16	AA59126/16XJ02
15-302-3-095	MIL-T-55155/16	M55155/16XI02	A-A-59126/16	AA59126/16XI02

Continued on next page...

MILITARY REFERENCE SPECIFICATIONS CONTINUED:

15-302-4-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-302-4-05	MIL-T-55155/16	M55155/16XH03	A-A-59126/16	AA59126/16XH03
15-302-4-088	MIL-T-55155/16	M55155/16XJ03	A-A-59126/16	AA59126/16XJ03
15-302-4-095	MIL-T-55155/16	M55155/16XI03	A-A-59126/16	AA59126/16XI03

TOOLING:

INSTALLATION TOOL: ARBOR PRESS	INSTALLATION TOOL: ANVIL (ARBOR PRESS OPERATED)	INSTALLATION TOOL: PRESS-FIT / ROLL SWAGE / RIVET PUNCH (ARBOR PRESS OPERATED)	INSTALLATION TOOL: FLARE SWAGE PUNCH (ARBOR PRESS OPERATED)
TM1	TA125-94-23	TP62-44	TFLP90-150

NOTES:

DATASHEET NOTES

N/A

INSTRUCTION NOTES

SEE GENERAL SWAGING INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE WWW.CONCORD-ELECTRONICS.COM