



**Part Number: 9538**

RS232, #24-8c, SR-PVC, O/A Foil, PVC Jkt, CMG

### Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	RS-232
------------------------	--------

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
24	7x32	TC - Tinned Copper	8

Conductor Count:	8
------------------	---

##### Insulation

Material	Nominal Wall Thickness
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011 in

##### Color Chart

Number	Color
1	Black
2	White
3	Red
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow

##### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.224 in	0.032 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
25 Ohm/1000ft	18 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield

33 pF/ft	65 pF/ft
----------	----------

#### Current

##### Max. Recommended Current [A]

Per conductor @ 25°C: 1.75 A

Current Table Note: 10C Temperature Rise

#### Voltage

##### UL Voltage Rating

300 V RMS

#### Temperature Range

UL Temp Rating: 80°C (UL AWM Style 2464)

Operating Temp Range: -30°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight: 31 lbs/1000ft

Max Recommended Pulling Tension: 44 lbs

Min Bend Radius/Minor Axis: 2.25 in

#### Standards

NEC Articles: 800

NEC/(UL) Specification: CMG

CEC/C(UL) Specification: CMG

UL AWM Style: 2464 (300 V 80°C)

CPR Euroclass: Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU: Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2005-04-01

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

#### Suitability

Suitability - Indoor: Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability: UL1685 FT4 Loading

CSA Flammability: FT4

ISO/IEC Flammability: IEC 60332-1-2

UL voltage rating: 300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N): No

#### Part Number

#### Variants

Item #	Color	UPC	Length	Footnote
9538.0030	Chrome		30 m	
9538.00U152	Chrome		152 m	
9538.00U305	Chrome		305 m	
9538.01152	Chrome		152 m	
9538.01305	Chrome		305 m	

9538 060100	Chrome	612825255345	100 ft	
9538 0601000	Chrome	612825255352	1,000 ft	C
9538 060500	Chrome	612825255369	500 ft	C
9538 0605000	Chrome	612825255376	5,000 ft	C
9538 060U1000	Chrome	612825255321	1,000 ft	
9538 060U500	Chrome	612825255338	500 ft	
9538.K1305	Chrome		305 m	

Footnote: C - CRATE REEL PUT-UP.

## History

Update and Revision:	Revision Number: 0.282 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.