



**Part Number: 9966**

Electronic, 2 C #22 Str TC, PVC-NYL Ins, OA TC Brd, PVC Jkt

[Request Sample](#)

## Product Description

Electronic, 2 Conductor 22AWG (19x34) Tinned Copper, PVC-NYL Insulation, Overall Tinned Copper Braid(90%) Shield, PVC Outer Jacket

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
22	19x34	TC - Tinned Copper	2

Conductor Count:	2
Total Number of Pairs:	1
Conductor Size:	22 AWG

#### Insulation

Layer	Material	Nominal Wall Thickness
1	PVC - Polyvinyl Chloride	0.01 in
2	Nylon	0.003 in

#### Color Chart

Number	Color
1	White
2	Black

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	90 %

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.174 in	0.02 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
14.6 Ohm/1000ft	6.2 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
52 pF/ft	87 pF/ft

#### Inductance

Nominal Inductance
0.129 µH/ft

#### Current

**Max. Recommended Current [A]**

2.8 Amps per conductor @ 25°C

**Voltage****Non-UL Voltage Rating**

600 V RMS

Electrical Characteristics Notes: 500 megohms/1000 ft. @ 500 VDC

**Temperature Range**

UL Temp Rating: 105°C

Operating Temp Range: -20°C To +105°C

**Mechanical Characteristics**

Bulk Cable Weight: 19 lbs/1000ft

Max Recommended Pulling Tension: 19 lbs

Min Bend Radius/Minor Axis: 1.75 in

**Standards**

CPR Euroclass: Eca

Military Specification: MIL-W-16878E/17 (insulated conductor)

Other Specification: NEMA HP3

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2005-10-01

CA Prop 65 (CJ for Wire &amp; Cable): Yes

MII Order #39 (China RoHS): Yes

**Flammability, LSOH, Toxicity Testing**

ISO/IEC Flammability: IEC 60332-1-2

**Plenum/Non-Plenum**

Plenum (Y/N): No

**Part Number****Variants**

Item #	Color	UPC	Footnote
9966 009100	White	612825265313	
9966 0091000	White	612825265320	C
9966 009500	White	612825265337	

Footnote: C - CRATE REEL PUT-UP.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.