


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- DIP Socket
- Number of Positions = 8
- Row-to-Row Spacing = 7.62 mm
- Thru Hole
- Mount Style = Vertical

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- [OPEN FRAME DIP, PREMIUM \(MACHINE CONTACT\), LEAD FR...](#)
(PDF, English)

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

[List all Documents](#)

- Product Type = DIP Socket
- Number of Positions = 8
- Profile = Standard
- Frame Style = Ladder
- Leg Style = Straight
- Sleeve Material = Copper
- Product Series = 800 Series

- Insulation Resistance ($M\Omega$) = 5,000
- Contact Resistance ($m\Omega$) = 10

- Termination (Solder) Post Length (mm [in]) = 3.18 [0.125]
- Solder Tail Contact Plating = Tin

- Row-to-Row Spacing (mm [in]) = 7.62 [0.300]
- Mount Style = Vertical
- Centerline (mm [in]) = 2.54 [0.100]

- Contact Mount = Thru Hole
- Contact Material = Beryllium Copper
- Contact Mating Area Plating Material = Tin
- Contact Style = Screw Machine
- Mating Contact Type = Four-Fingered

- Height Above PC Board (mm [in]) = 2.67
[0.105]

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Temperature Range ($^{\circ}\text{C}$) = 105

- Packaging Method = Tube

- Brand = Tyco Electronics