

RSS3W4K7JTB

✓ ACTIVE

CGS | CGS RSS

TE Internal #: 3-1624246-7
4.7K ohm, Metal Oxide Film, Power Resistor, 5 %, 3 W, ±300 ppm/°C, Axial-Leaded, Copper Termination, 15 x 5 mm, Ammo Packed, 2 Terminations, CGS RSS

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Metal Oxide Film**
Power Rating: **3 W**
Resistance Class: **1kΩ – 1MΩ**
Resistance Value: **4.7K Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	350 V
Power Rating	3 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	4.7K Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	15 x 5 mm
------------------------------	-----------



Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±300 ppm/°C

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RSS3W4K7JTB

4.7K ohm, Metal Oxide Film, Power Resistor, 5 %, 3 W, ±300 ppm/°C, Axial-Leaded, Copper Termination, 15 x 5 mm, Ammo Packed, 2 Terminations, CGS RSS



TE Part # 1-1624246-4
RSS3 1K2 5% AMMO PK



TE Part # 1624246-5
RSS3 12K 5% AMMO PK



TE Part # 1879004-5
RSS7 33K 5% LOOSE



TE Part # 3-1624246-8
RSS3 560R 5% AMMO PK




TE Part # 4-1624246-9
RSS3 8K2 5% AMMO PK

Also in the Series | CGS RSS



Connector Hardware(1)



Duct Seals(4)




PCMCIA Connectors(1)




Through-Hole Resistors(63)


Customers Also Bought



TE Part #316915-1
Z-STACK CONN 240P F16 ASSY



TE Part #536565-3
2MMFB,SHRD,096,SIG,HDR



TE Part #6-1437167-0
FSP-23Z-5



TE Part #1622854-1
CRG0603 1% 15R




TE Part #1623749-3
ER17 15R 5% LOOSE



TE Part #3-1879351-6
RR01 5% 82K AMMO



TE Part #4-1474671-1
FSP-28Z-4



TE Part #1546097-3
5.08 HORIZ HDR CLOSEDEND 3 POS



Documents

Product Drawings

RSS3 4K7 5% AMMO PK

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1624246-7_BA1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_3-1624246-7_BA1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1624246-7_BA1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

High Voltage Resistors - Type RSS Series - Tyco Electronics Passives

English