

Type BDS100 Series



With less than 40nH inductance and a 100Watt power rating in an easy-mounting 38mm x 25mm Isotop case, the BDS100 offers high power density over a wide range of ohmic values (R47 – 1M Ω) and benefits from 10 years experience in the field.

Available in 6 resistor configurations with 2 or 4 easy to connect terminals, the resistors are made from quality materials for optimum reliability and stability with very low partial discharge.

Tyco can test resistors to conform to relevant customer specifications, and will advise on the use of resistors for pulse energy and high voltage applications (HV designs available). Resistors with alternative terminations or flying leads are available, and custom designs are welcome.

This product is available via distribution.

Key Features

- **100W in a 9.5cm² footprint**
 - Gives an impressive power density of 10.5W/cm²
- **Virtually inductance-free**
 - Inductance < 40nH
- **Wide resistance range:** 0.47 Ω to 1M Ω
 - Coupled with 1% tolerance gives ultimate design flexibility
- **Multiple terminal configurations and multi-resistor packages**
 - The space saving solution
- **Partial discharge <10pC at 2kV**
 - Guaranteeing quality, reliability and long life

Thick Film Power Resistors

Type BDS100 Series

Characteristics - Electrical

Resistance Range:	R47 - 1M Ω	
Resistance Tolerance:	$\pm 10\%$, 5% (Tighter by discussion)	
TCR:	R<1 Ω R>1 Ω	$\pm 250\text{ppm}/^\circ\text{C}$ $\pm 150\text{ppm}/^\circ\text{C}$
Rated Power:	Heatsink: 115 $^\circ\text{C}$ / 100 $^\circ\text{C}$ / 60 $^\circ\text{C}$	25W / 50W / 100W
Capacitance:	Parallel	15pF To Earth 40pF
Series Inductance:	40nH (Maximum)	
Limiting Element Voltage:	(100W or Less)	500Vdc/ac rms
Isolating Voltage:	(Terminal to Heatsink)	2.5kVac rms
Single Shot Voltage:	1.5/50ms	4kV
Insulation Resistance:	(at 500V dc)	>100G Ω
Partial Discharge:	at 2kV	<10pC
Heat Dissipation:	Although the use of proprietary heat sinks with lower thermal resistance is acceptable, up rating is not recommended. The use of proprietary heat sink compound to improve thermal conductivity is essential.	


Characteristics - Environmental

Endurance (Rated Power):	2000cyc. at P _{Rated}	ΔR 0.25% Typ
Humidity Load Life:	56 Days, 40 $^\circ\text{C}$, 95% RH	ΔR 0.25% Typ (I.R.>10G Ω)
Temperature Cycling:	-55 $^\circ\text{C}$ to +125 $^\circ\text{C}$, 5cycles	ΔR 0.25% Typ
Operating Storage Temp:	-55 $^\circ\text{C}$ to +125 $^\circ\text{C}$	
Short Term Overload:	3 x P _{Rated} (10s)	ΔR 0.25% Typ
Vibration:	10/500Hz	ΔR 0.25% Typ
Bump:	40g 4000 bumps	ΔR 0.25% Typ

Characteristics - Mechanical

Terminal Size:		M4
Terminal Torque (max.):		1.3Nm
Creepage Distance:		10mm
Clearance:	Terminal to Heatsink	10mm
	Terminal to Terminal	3mm
Heatsink Surface Finish:	R ^a	< 6μm
Heatsink Flatness:		0.05mm
Weight:		35g

Dimensions



Applications

- Snubbing (Low inductance)
- High Voltage
- Balancing Resistor (Multi-resistor package)
- High Frequency
- Filter (Low inductance)

Type BDS100 Series

Terminal Circuit Type

A (Standard)




B (Voltage Sense)




C (Special)




D (Isolated)




E (Network Tapped)




F (Network 3 Res.)



Derating Curve



Pulse Energy



How to Order

BDS 2	A	100	1K0	J
Common Part	Circuit Type	Power Dissipation	Resistance Value	Tolerance
BDS 2 (2 Terminal) BDS 4 (4 Terminal) BDH 2 (2Term. High Voltage) BDH 4 (4 Term. High Voltage)	A: Standard B-F: See above	100 - 100 Watts at 70°C	0.6Ω (600mΩ) R60 1Ω (1000mΩ) 1R0 1KΩ (1000Ω) 1K0 1MΩ (1000000Ω) 1M0	F - 1% J - 5% K - 10%