


Sleeves for Wire and Cable Identification

▶ 3-TO-1 SHRINK RATIO TWO-SIDED PRINTABLE PERMASLEEVE™ WIRE MARKERS



PermaSleeve full-circle markers are available in a 3-to-1 shrink ratio to cover a wider range of wire diameters per sleeve size.

White Polyolefin (B-342) Two-Sided Printable PermaSleeve Markers

Part Number	Markers Per Box	Range of Wire Dia. Inch (mm)		Approx. Wire Gauge*	Marker Width Inch (mm) A	Marker Height Inch (mm) B	Vertical Repeat Inch (mm) C	Maximum Lines of Print	Maximum Characters Across				
		Min.	Max.						5 CPI	10 CPI	17.1 CPI		
2.000" Marker Width													
3PS-094-2-WT	2,500	0.023	(0.58)–(0.080 (2.03)	28-18	2.000 (50.80)	0.182 (4.60)	0.500 (12.70)	1	9	18	30		
3PS-094-2-WT-S	500	0.023	(0.58)–(0.080 (2.03)	28-18	2.000 (50.80)	0.182 (4.60)	0.500 (12.70)	1	9	18	30		
3PS-125-2-WT	2,500	0.046	(1.17)–(0.110 (2.79)	22-16	2.000 (50.80)	0.235 (6.00)	0.500 (12.70)	1	9	18	30		
3PS-125-2-WT-S	500	0.046	(1.17)–(0.110 (2.79)	22-16	2.000 (50.80)	0.235 (6.00)	0.500 (12.70)	1	9	18	30		
3PS-187-2-WT	2,500	0.062	(1.57)–(0.150 (3.81)	18-12	2.000 (50.80)	0.335 (8.50)	0.625 (16.00)	2	9	18	30		
3PS-187-2-WT-S	500	0.062	(1.57)–(0.150 (3.81)	18-12	2.000 (50.80)	0.335 (8.50)	0.625 (16.00)	2	9	18	30		
3PS-250-2-WT	2,500	0.094	(2.39)–(0.215 (5.46)	16-10	2.000 (50.80)	0.439 (11.15)	0.750 (19.05)	2	9	18	30		
3PS-250-2-WT-S	500	0.094	(2.39)–(0.215 (5.46)	16-10	2.000 (50.80)	0.439 (11.15)	0.750 (19.05)	2	9	18	30		
3PS-375-2-WT	1,000	0.125	(3.18)–(0.320 (8.13)	12-6	2.000 (50.80)	0.645 (16.40)	1.000 (25.40)	4	9	18	30		
3PS-375-2-WT-S	250	0.125	(3.18)–(0.320 (8.13)	12-6	2.000 (50.80)	0.645 (16.40)	1.000 (25.40)	4	9	18	30		
3PS-500-2-WT	500	0.187	(4.75)–(0.450 (11.43)	8-1	2.000 (50.80)	0.851 (21.60)	1.250 (31.75)	5	9	18	30		
3PS-500-2-WT-S	250	0.187	(4.75)–(0.450 (11.43)	8-1	2.000 (50.80)	0.851 (21.60)	1.250 (31.75)	5	9	18	30		

*Based on National Electric Code insulation measurement of THHN wire.

Sleeves may be perforated at factory for shorter marker lengths. Depending on overall length, sleeves may be perforated in halves, thirds or fourths. Contact your Brady Identification Solutions Distributor or Customer Service Representative for ordering information.