


BMP®41 Materials

BradyID.com/s36

Self-Laminating Vinyl Wire and Cable Labels (B-427)

Labels feature a clear, non-printable area that wraps around print-on area to protect text. Vinyl material offers superior resistance to handling, solvents, oil, grease, dirt and water. Temp. range -40° F to 158° F (-40° C to 70° C), UL recognized.




Fits Printers	Figure	Catalog#	Color	Approx. Wire Gauge	Max Wire Dia. Inch (mm)	Label Width A Inch (mm)	Label Height B Inch (mm)	Print-On Height C Inch (mm)	Labels Per Roll	Sized To Fit	Ribbon in Cartridge
BMP41, 51, 53	Fig. 32	M-11-427	BK on WT	16 to 10	0.160 (4.1)	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	360	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 32	M-136-427	BK on WT	16 to 10	0.160 (4.1)	1.000 (25.4)	0.750 (19.1)	0.375 (9.5)	340	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 42b	MC-750-427	BK on WT	16 to 10	0.270 (6.7)	25 ft. (7.6 m)	0.750 (19.1)	0.375 (9.5)	1 roll (cont.)	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 32	M-47-427	BK on WT	12 to 10	0.210 (5.3)	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	360	2 pair Fiber/Coaxial, Single/Multi-Mode	R4300
BMP41, 51, 53	Fig. 32	M-48-427	BK on WT	12 to 10	0.210 (5.3)	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	200	CAT-6, 4 pair UTP Copper, Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-49-427	BK on WT	12 to 10	0.210 (5.3)	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	260	2 pair Fiber/Coaxial, Single/Multi-Mode	R4300
BMP41, 51, 53	Fig. 32	M-102-427	BK on WT	10 to 4	0.270 (6.7)	0.500 (12.7)	1.250 (31.7)	0.375 (9.5)	200	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 32	M-143-427	BK on WT	10 to 4	0.270 (6.7)	1.000 (25.4)	1.250 (31.7)	0.500 (12.7)	200	CAT-6, 4 pair UTP Copper, Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-89-427	BK on WT	10 to 4	0.320 (8.1)	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	180	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 32	M-90-427	BK on WT	10 to 4	0.320 (8.1)	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	180	CAT-6, 4 pair UTP Copper	R4300
BMP41, 51, 53	Fig. 32	M-91-427	BK on WT	10 to 4	0.320 (8.1)	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	180	CAT-6, 4 pair UTP Copper, Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-61-427	BK on WT	3 to 20	0.530 (13.5)	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	110	25 pair Copper, 4-12 pair Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-53-427	BK on WT	30 to 400 kcmil	0.850 (21.6)	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	70	50 pair Copper, 24 pair Fiber, Backbone	R4300
BMP41, 51, 53	Fig. 32	M-91-427-YL	BK on YL	10 to 4	0.320 (8.1)	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	180	CAT-6, 4 pair UTP Copper, Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-51-427-YL	BK on YL	3 to 20	0.530 (13.5)	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	110	25 pair Copper, 4-12 pair Fiber, Coaxial	R4300
BMP41, 51, 53	Fig. 32	M-53-427-YL	BK on YL	30 to 400 kcmil	0.850 (21.6)	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	70	50 pair Copper, 24 pair Fiber, Backbone	R4300

PermaSleeve® PS Polyolefin Wire Markers (B-342)

Military / industrial grade sleeves offer the ultimate in marker durability, permanence and aesthetic appearance. 3:1 heat-shrinkable markers fit snugly around wires, are fade-resistant and flame-retardant. Temp range: -67° F to 275° F (-55° C to 130° C), RoHS compliant and UL recognized.

- Meets specifications:**
- SSAE-AS-23053/5
 - SAE-AS-81531

- Tested per:**
- ASTM E162
 - ASTM E662
 - MIL-STD-202




Fits Printers	Figure	Catalog #	B#	Color	Approx. Wire Gauge	Wire Diameter Range Inch (mm)	Supplied Diameter B Inch (mm)	Supplied Width A Inch (mm)	Sleeves Per Roll	Ribbon in Cartridge
BMP41, 51, 53	Fig. 44	* M-125-075-342	B-342	BK on WT	22 to 16	0.046 - 0.110 (1.2 - 2.8)	0.235 (5.9)	0.750 (19.1)	80	R4300
BMP41, 51, 53	Fig. 58	* MC-125-342	B-342	BK on WT	22 to 16	0.046 - 0.110 (1.2 - 2.8)	0.235 (5.9)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 44	* M-187-075-342	B-342	BK on WT	20 to 10	0.062 - 0.150 (1.6 - 3.8)	0.335 (8.5)	0.750 (19.1)	80	R4300
BMP41, 51, 53	Fig. 58	* MC-187-342	B-342	BK on WT	20 to 10	0.062 - 0.150 (1.6 - 3.8)	0.335 (8.5)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 44	* M-250-075-342	B-342	BK on WT	16 to 8	0.094 - 0.215 (2.4 - 5.5)	0.439 (11.1)	0.750 (19.1)	80	R4300
BMP41, 51, 53	Fig. 58	* MC-250-342	B-342	BK on WT	16 to 8	0.094 - 0.215 (2.4 - 5.5)	0.439 (11.1)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 44	* M-375-075-342	B-342	BK on WT	12 to 4	0.125 - 0.320 (3.2 - 8.1)	0.645 (16.4)	0.750 (19.1)	80	R4300
BMP41, 51, 53	Fig. 58	* MC1-375-342	B-342	BK on WT	12 to 4	0.125 - 0.320 (3.2 - 8.1)	0.645 (16.4)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 58	* MC-125-342-YL	B-342	BK on YL	22 to 16	0.046 - 0.110 (1.2 - 2.8)	0.235 (5.9)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 58	* MC-187-342-YL	B-342	BK on YL	20 to 10	0.062 - 0.150 (1.6 - 3.8)	0.335 (8.5)	7 ft. (2.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 58	* MC-250-342-YL	B-342	BK on YL	16 to 8	0.094 - 0.215 (2.4 - 5.5)	0.439 (11.1)	7 ft. (2.1 m)	1 roll (cont.)	R4300

* **WARNING:** Cancer www.P65Warnings.ca.gov

Nylon Cloth Cable Flags (B-499)

Pre-formatted with two printable areas, allowing flag to be easily folded around wire to create a two-sided, printed flag. Nylon Cloth with permanent adhesive is pliable for rough or smooth surfaces. Temp. range: -94° F to 194° F (-70° C to 90° C). UL recognized.



Fits Printers	Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Non-Print Area Inch (mm)	Labels Per Roll	Ribbon in Cartridge
BMP41, 51, 53	Fig. 63	M-141-499	B-499	Nylon Cloth	BK on WT	1.000 (25.4)	1.000 (25.4)	0.250 (6.3)	90	R4300

Portable Printers

BMP41