

# Specifications

## Eaton CL1208-4-100TR-R

Eaton CL1208 inductor, 100 nH, 0.45 mΩ resistance, Four-phase



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton CL1208 inductor
<b>CATALOG NUMBER</b>	CL1208-4-100TR-R
<b>UPC</b>	051712533737
<b>PRODUCT LENGTH/DEPTH</b>	24 mm
<b>PRODUCT HEIGHT</b>	8 mm
<b>PRODUCT WIDTH</b>	11.5 mm
<b>PRODUCT WEIGHT</b>	8.32 g
<b>COMPLIANCES</b>	RoHS Compliant



### Product specifications

**TYPE** Multi-phase coupled inductor

### Resources

**CATALOGS** [Magnetics short form catalog](#)

<b>MOUNTING</b>	SMT
<b>PHASE</b>	Four-phase
<b>ISAT</b>	18 A
<b>PACKAGE QUANTITY</b>	200
<b>MATERIAL</b>	Ferrite
<b>CONTACT CONFIGURATION</b>	Four-pin
<b>TEMPERATURE RATING</b>	-40 to 125 °C
<b>RESISTANCE</b>	0.45 mΩ
<b>TERMINALS</b>	Four
<b>INDUCTANCE</b>	100 nH
<b>SERIES</b>	CL1208

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - CL1208-4-100TR-R](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
 All other trademarks are property of their respective owners.

