

# Specifications

## Eaton MCL2V0603-101-R

IND, MCL2V0603, 100nH, 60mA, 4Ω, SMT, 101-R



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton MCL chip inductor
<b>CATALOG NUMBER</b>	MCL2V0603-101-R
<b>UPC</b>	051712772433
<b>PRODUCT LENGTH/DEPTH</b>	0.63 mm
<b>PRODUCT HEIGHT</b>	0.33 mm
<b>PRODUCT WIDTH</b>	0.33 mm
<b>PRODUCT WEIGHT</b>	0.00022 g
<b>COMPLIANCES</b>	RoHS Compliant



### Product specifications

**TYPE** Chip inductor

### Resources

<b>MOUNTING</b>	SMT
<b>IRMS</b>	0.06 A
<b>PACKAGE QUANTITY</b>	15000
<b>CONTACT CONFIGURATION</b>	Two-pin
<b>TEMPERATURE RATING</b>	125 °C max
<b>RESISTANCE</b>	4000 mΩ

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - MCL2V0603-101-R</a>
<b>TECHNICAL DATA SHEETS</b>	<a href="#">MCL2V0603 Multilayer chip inductor</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

