


D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	4pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: DIN 40050-9	IP 69K, in mated condition
Temperature range: IEC 60664-1	-30°C ... +105°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PP GF, UL 94
Sealing:	FPM
Coupling nut:	1.4404 stainless steel
Moulding body:	Thermoplastic elastomere, grey

Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:

1)	brown
2)	white
3)	blue
4)	black

Part no:	Description:	Length L:	Cable:
43-10512	SAL - FB - 12 - RK4 - 2 / P1	2m	PP, orange, 4x0,34mm ² Cable: 781-P13400
43-10513	SAL - FB - 12 - RK4 - 3 / P1	3m	
43-10514	SAL - FB - 12 - RK4 - 5 / P1	5m	
43-10515	SAL - FB - 12 - RK4 - 10 / P1	10m	
43-xxxxx	SAL - FB - 12 - RK4 - ... / P1	x	

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: a 21.02.11 VF Ä3909 technical specification changed, part no. cable in table added, data sheet modified	 dim. in mm		title: Female connector M12x1 axial, FB	
			date	name		
		tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	08.03.07	Fromm	dwg no: 43K1A075
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	appd.	08.03.07	Mankopf	
						part no: see table