


RFTERMSMAJ1W Datasheet

Product Name // SMA Jack Termination (1W)

 [View Product Page](#)



// Product Description:

- | | |
|--|--|
|  SMA Jack Termination (1W) |  Dielectric withstanding Voltage: >750V |
|  Maximum Voltage: 335V |  Impedance: 50Ohm |
|  Temperature range: -65°C to +165°C |  Body Material: Stainless Steel Passivation |
|  Frequency range: 0GHz - 18GHz |  Contact Material: Beryllium Copper |
|  VSWR: <1.15 | |

// General Information:

Product Display Title:	RF Termination Series SMA
Product Family:	Radio Frequency Connectors
Product Series:	RF Termination Series
Average Power:	<1W
Body Length:	13.00mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Dielectric Withstanding Voltage:	>750V
Durability:	>500 cycles
Function:	Female RF Termination
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710
Max Operating Temperature:	+165°C
Min Operating Temperature:	-65°C
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Thread Size:	1/4 36UNS 2A
Voltage Max:	335V
Vswr:	<1.15

// Product PDF Links

 [RF Termination Series Product...](#)

// Product 3D CAD Model Links

 [RFTERMSMAJ1W3D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)