







Technical specification:

Rated voltage: IEC 61076-2-104	3pos 60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque M12x1:	0,6 Nm
Recommended torque M8x1:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220 Insert across flats 9: 36-000210

Conact assignment:

1	brown	—
3	blue	—
4	black	—

Part no:	Description:	Length L:	Cable:
43-11450	SAL - 12 - RS3 - 8 - RK3 - 0,3 / K1	0,3m	TPU, UL 20549, black, 3x0,25mm ² Cable: 781-K12300
43-11451	SAL - 12 - RS3 - 8 - RK3 - 0,6 / K1	0,6m	
43-11452	SAL - 12 - RS3 - 8 - RK3 - 1,5 / K1	1,5m	
43-11453	SAL - 12 - RS3 - 8 - RK3 - 3 / K1	3m	
43-xxxxx	SAL - 12 - RS3 - 8 - RK3 - ... / K1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: b 09.02.11 VF Ä3767 Coupling nut/ screw modified, spanner flats added, data sheet modified	 dim. in mm		title: Connecting cable M12x1/ M8x1, male connector axial - female connector axial	
			date	name		
		tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	03.01.08	Franz	dwg no: 43K1A587
			appd.	03.01.08	Mankopf	
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table