



## TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)

### TD229-1202S=TDFR 12 SEC M83726/29-1202S

CII

TD229-1202S

TE Internal Number: 1617808-5

Not EU RoHS or ELV Compliant

[Find Compliant Alternatives](#)

Type of Control **Fixed**

Input Voltage (VDC) **28**

Contact Current Rating (A) **10A@28VDC, 115VAC**

Mode of Operation **Delay on Release**

Delay Time **12 Seconds**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

#### Product Type Features

Relay Type

**Time Delay**

Product Category

**Electromechanical Relays**

Enclosure Type

**Hermetic Sealed Metallic**

Product Type

**Relay**

#### Configuration Features

Multiple Timing Ranges

**Without**

#### Electrical Characteristics

Input Voltage (VDC)

**28**

Actuating System

**DC**

#### Contact Features

Type of Control

**Fixed**

Contact Current Rating (A)

**10A@28VDC, 115VAC**

Delay Time

**12 Seconds**

Contact Arrangement

**2 Form C, DPDT, 2 C/O**

#### Termination Features

Termination Type

**Solder Hook Terminal**

---

Mechanical Attachment	Mounting Type	<b>Raised Vertical Flange Mount</b>
Dimensions	Dimensions (L x W x H) (Approximate)	<b>25.79 x 25.79 x 25.4 mm [ 1.015 x 1.015 x 1 in ]</b>
Usage Conditions	Operating Temperature Range (°C)	<b>-55 – 125</b>
Operation/Application	Mode of Operation	<b>Delay on Release</b>
Other	Repeatability (Max)	<b>±10%</b>

---

Product Compliance

[Statement of Compliance](#)  
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)