


3SBC1650A2 Product Details

SharePrintEmail



Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ?

3SBC 1/5 - Size Relay Series
- ?

Input Voltage = 26.5 VDC
- ?

Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ?

Contact - Rated Current = 2 A
- ?

Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ?

[Check Pricing & Availability](#)
- ?

[Search for Tooling](#)
- ?

[Product Feature Selector](#)
- ?

[Contact Us About This Product](#)

3SBC1650A2
(4 - 1617072 - 8)

TE Internal Number: 4 - 1617072 - 8

 [Active](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ?Series = 3SBC 1/5 - Size Relay ? Termination Type = Solder Hook Terminals Electrical Characteristics: ? Input Voltage (VDC) = 26.5 ? Contact - Rated Current (A) = 2 ? Coil Polarity Protection Diode = Without ? Transistor Driver = Without ? Coil Resistance (?) = 1350 ? MOSFET Driver = Without ? Coil Power Measurement = Milliwatts ? Coil - Rated Power (mW) = 520 ? Actuating System = DC ? Shock = 75 G's, 6ms ? Vibration = 30G's, 10 to 3000Hz Contact Features: ? Mounting Options = Panel Mount ? Enclosure Type = Hermetically Sealed	Configuration Features: ?Contact Arrangement = 2 Form C, DPDT, 2 C/O ? Coil - Magnetic System = Non Polarized, Monostable ? Coil Suppression Diode = With Industry Standards: ? Government/Industry Qualification = Yes ? Government/Industry Part Number = M39016/37 -023M ?RoHS/ELV Compliance = Not ELV/RoHS compliant ?Lead Free Solder Processes = Not suitable for lead free processing ? Approved Standards = M39016 Qualified, M Level Conditions for Usage: ? Temperature Range (°C) = -65 - +125 Other: ? Brand = CII

Contact Features:

?

Mounting Options = Panel Mount

?

Enclosure Type = Hermetically Sealed

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events
& Technology Updates

Enter your email address

