




NO.	MASSE / DIM
D1 (+0 -0.15)	34.2
D2 (H13)	3.2
D3 (MAX)	29
E (± 0.1)	29.4
L1 (MAX)	34.1
L2 (+0.4 -0)	19
L3 (± 0.2)	4
L4 (± 0.3)	38

NO	NOTE
1	SPECIFICATION AND DIMENSIONS ARE SUBJECT TO CHANGE
2	DRAWING ILLUSTRATE NORMAL INSULATOR POSITIONING



Material Specification:
Shell Material: Aluminium alloy
Shell Plating: Chromate over Cadmium, olive drab
Insulator Material: Chloroprene rubber
Contact Material: Copper alloy
Contact Plating: Silver

all dimensions are in mm Dimensions without tolerance indications are general tolerances in acc. with ISO2768-FH		drawing for CUSTOMER	
 ITT <i>Engineered for life</i> <small>ITT Cannon Veam Italy S.r.l. 20020 Lainate (MI), Italy</small>	description CIR02R-20-3S-F80		
	Front mounting receptacle through mounting holes no endbell Crimp for AWG wire (used in F80 insert) / Socket / Layout: 20-3		
© All rights reserved. Reproduction or issue to third in any form whenever is only permitted with written authorization of ITT Cannon		page 1/1	revision 3616 18. Oct 19