

Specifications



Eaton 16290-2

Eaton Bussmann series power terminal block, 600 Vac, 600 Vdc, 150 A, Two-pole, 1/4 Inches-20 TPI X 3/4 Inches Stud (Line/Load), SCCR: 10 kA, Black, Molded Thermoplastic Base, Tin-plated aluminum connector

General specifications

PRODUCT NAME	Eaton Bussmann series power terminal block
CATALOG NUMBER	16290-2
UPC	051712502306
PRODUCT LENGTH/DEPTH	2.84 in
PRODUCT HEIGHT	1.8 in
PRODUCT WIDTH	1.85 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	Not Applicable
COMPLIANCES	Contact factory RoHS Compliant
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	150A
SHORT-CIRCUIT RATING	SCCR: 10 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

General information

CONNECTION	1/4 In-20 TPI X 3/4 In Stud (Line/Load)
-------------------	--

Physical details

COLOR	Black
MATERIAL	Molded thermoplastic base, tin plated aluminum connector
NUMBER OF POLES	Two-pole
TYPE	Power terminal block

Resources

	Bussmann series complete full line catalog no. 1007
CATALOGS	16290-2-POWER DIST. STUD BLOCK
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2414
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 16290-2

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.