



EMI & EMC Solutions > EMC Filters > Power Line Filters > 3-Phase Filters > 3 Phase General Purpose EMI Filters, KES



Current Rating: 3 A

Input Termination Type: FASTON

Output Termination Type: .250" FASTON

Wiring Configuration: WYE (4 wire + ground)

Operating Voltage: 440 VAC

[All 3 Phase General Purpose EMI Filters, KES \(64\)](#)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	FASTON
Output Termination Type	.250" FASTON

Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	3
Current Rating	3 A
Operating Voltage	440 VAC

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | Corcom KES

3KES1AFPW

3 A 3-Phase Filter, FASTON Input, .250" FASTON Output, WYE (4 wire + ground), 440 VAC, Chassis Mount, Corcom KES



3-Phase Filters(64)

Customers Also Bought

TE Part #NB07552001
HTAT-16/4-0-STK

TE Part #822036-SF
FN3256H-8-29-R69

TE Part #806157-SF
FN3280H-8-29

TE Part #3-640441-3
03P MTA100 CONN ASSY WHT

TE Part #7-1393243-5
RT424110

TE Part #7-1393243-9
RT424730

TE Part #CAT-F83-KES
3 Phase General Purpose EMI Filters,
KES

TE Part #1622185-1
LR0204 1% 1K5

TE Part #1658526-5
609-1041LF FEM SOCKET, LEAD FREE

Documents

Product Drawings

KES 3A 1S SPADE WYE 440VAC

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1609966-1_B.3d_igs.zip

English

Customer View Model

3KESS1AFPW

3 A 3-Phase Filter, FASTON Input, .250" FASTON Output, WYE (4 wire + ground),
440 VAC, Chassis Mount, Corcom KES



[ENG_CVM_CVM_1-1609966-1_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1609966-1_B.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KES SERIES](#)

English