

2-1609109-8 Product Details

[Share](#) [Print](#) [Email](#)



2-1609109-8
(PM000SZ6C)

TE Internal Number: 2-1609109-8

Active

[View 3D PDF](#)

EMI/RFI Filters and Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Filter - EMI/RFI
- Filter Type = Power Entry (Filtered/Unfiltered)
- P (3-10 Amp) Series
- High Performance Application, Switching Power Supply Application
- Mount Style = Mounting Ears (Vertical)

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CUSTOMER DRAWING PM000SZ6C \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [1-1654250-1 CORCOM EMI RFI QRG \(PDF, English\)](#)
- [5-1773450-6 CORCOM HIGH PERFORMANCE P SERIES WITH VE... \(PDF, English\)](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version B\)](#)
- [3D Model \(IGES, Version B\)](#)
- [3D Model \(STEP, Version B\)](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insertion Loss/Specifications](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Filter - EMI/RFI
- [Filter Type](#) = Power Entry (Filtered/Unfiltered)
- [Series](#) = P (3-10 Amp)
- [Filtered](#) = Yes
- [Type of Connector](#) = IEC 320/C-14

Mechanical Attachment:

- [Shield Style](#) = Complete can

Electrical Characteristics:

- [Input Voltage Select](#) = Single AC Voltage
- [Current Rating \(A\)](#) = 6
- [Voltage Selection](#) = Single
- [Voltage ≤ \(VAC\)](#) = 250
- Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (mA) = 0.5
- Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (mA) = 0.25

Termination Features:

- [Terminal Input - Output Combination](#) = IEC - 1/4" Faston

Body Features:

- [Mount Style](#) = Mounting Ears (Vertical)
- [Switch Type](#) = No Switch

Configuration Features:

- [Extender Options](#) = None
- [Fuse Options](#) = Single
- [Fuse Holder Type](#) = Selectable

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [Approved Standards](#) = UL Recognized, VDE Approved, CSA Certified

Operation/Application:

- [Application](#) = High Performance, Switching Power Supply

Other:

- [Brand](#) = Corcom
- [Comment](#) = Fits 1U high enclosure.

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

