

## RXEF075-2 Product Details



RXEF075-2

TE Internal Number: D61539-000

[Active](#)

### PolySwitch Resettable Devices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Radial Application
- Vmax = 72 V
- Imax = 40 A
- Family Name = RXEF
- Radial Construction

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [CP CATALOG 2011-RADIAL-LEADED](#) (PDF, English)

#### Product Specifications:

- [RXEF075](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- UL File Number = E74889
- CSA File Number = A78165

#### Electrical Characteristics:

- Vmax (V) = 72
- Imax (A) = 40
- [IH \(Room Temperature\) \(A\)](#) = 0.75
- [IT \(Room Temperature\) \(A\)](#) = 1.50
- [Rmin \(Ω\)](#) = 0.25
- [Rmax \(Ω\)](#) = 0.400
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.60
- Power Dissipation (Typical) (W) = 0.92

#### Termination Features:

- Construction = Radial

#### Body Features:

- Lead Type = Standard Kinked Lead

#### Contact Features:

- Family Name = RXEF

#### Configuration Features:

- Coating = Coated

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = Available on request (per IEC 60730-1)

#### Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

#### Operation/Application:

- Application = Radial

#### Packaging Features:

- Packaging Method = Tape & Reel

#### Other:

- Brand = Raychem

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

