



NANOSMDC200F-2 Product Details

[Share](#) [Print](#) [Email](#)


NANOSMDC200F-2
(RF1989-000)

TE Internal Number: RF1989-000

 [Active](#)

PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Vmax Operating = 6 V
- Vmax = 6 V
- Imax = 100 A
- Family Name = nanoSMD

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT](#) (PDF, English)

Product Specifications:

- [nanoSMDC200F](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL File Number = E74889
- CSA File Number = CA78165

Electrical Characteristics:

- [Vmax Operating \(V\)](#) = 6
- Vmax (V) = 6
- Imax (A) = 100
- [IH \(Room Temperature\) \(A\)](#) = 2
- [IT \(Room Temperature\) \(A\)](#) = 4.00
- [Rmin \(Ω\)](#) = 0.02
- [Rmax \(Ω\)](#) = 0.072
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.072
- Power Dissipation (Max) (W) = 1

Termination Features:

- Construction = Surface Mount

Contact Features:

- Family Name = nanoSMD

Configuration Features:

- [Form Factor \(inches\)](#) = 1206
- [Form Factor \(mm\)](#) = 3216

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041439

Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

