


|                        |                                    |
|------------------------|------------------------------------|
| <b>DRAWING NUMBER:</b> | <b>09-7184-2B-XX</b>               |
| <b>PRODUCT GROUP:</b>  | TERMINALS                          |
| <b>SUB-GROUP:</b>      | COMMERCIAL NON-INSULATED TERMINALS |
| <b>DESCRIPTION:</b>    | NON-INSULATED SLOTTED TERMINAL     |



| BOARD / PANEL MOUNTING METHOD | MOUNTING HOLE SIZE | DRILL SIZE | FEED THRU COMBINATION |
|-------------------------------|--------------------|------------|-----------------------|
| RIVET MOUNT                   | 0.044" $\pm$ 0.002 | #57        | N/A                   |

**PART NO. STRUCTURE:**

09-7184 - 2B - XX  
 PART SERIES    DIMENSION    FINISH

**MATERIAL OPTIONS:**

09-7184-2B-XX

| COMPONENT | MATERIAL | MATERIAL AND SPECIFICATION                  |
|-----------|----------|---|
| TERMINAL  | BRASS    | BRASS PER ASTM B453, ALLOY C35300, 1/2 HARD |

**DIMENSION OPTIONS:**

09-7184-2B-XX

| DIMENSION | A   | D   | PIN DIAMETER | OVERALL LENGTH | SHANK LENGTH (L) | BOARD/PANEL THICKNESS |
|-----------|-----|-----|--------------|----------------|------------------|-----------------------|
| 2B        | N/A | N/A | N/A          | 0.309" REF.    | 0.097"           | 9/128"                |

FINISH - PLATING OPTIONS:

09-7184-2B-XX

| FINISH CODE | COMPONENT | FINISH             | FINISH AND SPECIFICATION  |
|-------------|-----------|--------------------|---|
| 01          | TERMINAL  | SILVER             | 0.000300"MIN. SILVER PER ASTM B700, TYPE 2, GRADE D WITH A NON-CHROMATE PRESERVATIVE TREATMENT      |
| 03          | TERMINAL  | GOLD               | 0.000010"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000050"MIN. NICKEL PER SAE-AMS-QQ-N-290    |
| 035         | TERMINAL  | GOLD               | 0.000050"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000050"MIN. NICKEL PER SAE-AMS-QQ-N-290    |
| 04          | TERMINAL  | ELECTRO-TIN        | 0.000300"MIN. ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418                  |
| 044         | TERMINAL  | BRIGHT ELECTRO-TIN | 0.000300"MIN. BRIGHT ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418           |
| 05          | TERMINAL  | ELECTRO-SOLDER     | 0.000300"MIN. ELECTRO-SOLDER PER SAE-AMS-P-81728 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418         |
| 088         | TERMINAL  | BRIGHT TIN-LEAD    | 0.000300"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418 |

TOLERANCES:\*

| DECIMAL | FRACTIONAL | ANGULAR | DRAWING ORIGATION DATE | LAST MODIFICATION DATE |
|---------|------------|---------|------------------------|------------------------|
| ± 0.005 | ± 1/64     | ± 5 °   | 9/15/2000              | 3/1/2017               |

\*All dimensions are in inches.

RoHS COMPLIANCE:

09-7184-2B-XX

| PART NUMBER    | RoHS COMPLIANT |
|----------------|----------------|
| 09-7184-2B-01  | YES            |
| 09-7184-2B-03  | YES            |
| 09-7184-2B-035 | YES            |
| 09-7184-2B-04  | YES            |
| 09-7184-2B-044 | YES            |
| 09-7184-2B-05  | NO             |
| 09-7184-2B-088 | NO             |

TOOLING:

| INSTALLATION TOOL:<br>ARBOR PRESS | INSTALLATION TOOL:<br>ANVIL<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>PRESS-FIT / ROLL SWAGE / RIVET PUNCH<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>FLARE SWAGE PUNCH<br>(ARBOR PRESS OPERATED) |
|-----------------------------------|---|--|---|
| TM1                               | TA09-7183   | TP200-0  | N/A   |

NOTES:

| DATASHEET NOTES |
|-----------------|
| N/A             |

Continued on next page...

**NOTES** CONTINUED:

**INSTRUCTION NOTES**

SEE GENERAL RIVETING INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE [WWW.CONCORD-ELECTRONICS.COM](http://WWW.CONCORD-ELECTRONICS.COM).