



Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Packaging Method: **Dual Pack**

Packaging Quantity: 1

Heat Resistance Temperature (Max): 150 °C

Features

Body Features

Color (Supplied)	Black, Gray
Material Systems Code	25

Usage Conditions

Heat Resistance Temperature (Max)	150 °C
-----------------------------------	--------

Packaging Features

Packaging Method	Dual Pack
Packaging Quantity	1

Other

Pot Life	90 minute
Curing Method	20 °C for 24 hr, 85 °C for 1 hr

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC













Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---


Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # EG4836-000 203W301-25L-G02-0	 TE Part # 463391-000 342A012-25-G03-0	 TE Part # CV7478-000 302A812-25-0	 TE Part # 806793-000 214A042-25-0
 TE Part # 820091-000 301A011-25-0	 TE Part # 811464-000 301A513-50-0	 TE Part # 806425-000 202E336-50-0	 TE Part # 879086-000 222K342-25-02-0
 TE Part # 5470284010 CONVOLEX-1-0-SP	 TE Part # 879291-000 223W102-25-0	 TE Part # 952223-000 202K232-25-11-0	 TE Part # 861780-000 202W312-25-0


TE Part # 833320-000
301A514-50-0




TE Part # 820287-000
341A015-25-0




TE Part # 966871-000
200W212-25-0




TE Part # D96192-000
203W301-25-01-0



TE Part # EF7172-000
222S121-25-UP-0



TE Part # 707290-000
382A012-25-00-0



TE Part # 596653-000
202W342-25-0



TE Part # CAT-R21-73107237
Heat Shrink Boots: Lipped, Straight


Customers Also Bought




TE Part #281917-000
AA-400-200-CE-SUPRHTR



TE Part #70A1-12-06-1-B
70A1-12-06-1-B



TE Part #5039254029
DR-25-3/4-0-SP




TE Part #878497-000
202K153-25-0




TE Part #ZPF000000000004586
901-20 B 27




TE Part #EM3665-000
C6A-26C444X814-9




TE Part #1218532-1
AMPLIMITE,ASY,RCPT,STD,109,1,GMT



TE Part #ZPF0000000000020305
P 135-6-18 A231



TE Part #10205211-00
XPC10-S107-5KPS



TE Part #1218533-1
RECEPT ASSY,25 POSN,AMPLIMITE

Documents



Product Drawings

[S1125-KIT-8](#)

English

Datasheets & Catalog Pages

[Adhesives Selection Guide](#)

English

[Solutions for Defense Applications Certified to VG Standards](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English