

DTS26F21-35PN [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Series III, DEUTSCH 38999

TE Internal #: YDTS26F21-35PNV001

79 Position Circular Connector, Cable-to-Panel, Sealable, Wire & Cable, Signal, Panel Mount, Electroless Nickel, Aluminum, N Code

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug: D38999, 21-35 Insert, Electroless Nickel Plating



Connector System: **Cable-to-Panel**

Connector Mounting Type: **Panel Mount**

Number of Positions: **79**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

[All Straight Plug: D38999, 21-35 Insert, Electroless Nickel Plating \(2\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Number of Positions	79
Number of Power Positions	0
Number of Signal Positions	79
Contacts Preloaded	No

Body Features

Shell Plating Material	Electroless Nickel
Shell Base Material	Aluminum
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No



Contact Features

Contact Current Rating (Max)	5 A
Reverse Gender	No
Contact Layout Arrangement	21 – 35
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Retention Type	Threaded
Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	21
Alignment Keyed	Clocking

Dimensions

Wire Size	28 – 22 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # YDTS23N21-35ZAV001
HERM RECP



TE Part # YDTS21N21-35DNV001
HERM RECP



TE Part # YDTS21H21-35ZNV001
HERM RECP



TE Part # YDTS24Y21-35DNV001
HERM RECP



TE Part # YDTS23Y21-35SNV001
HERM RECP



TE Part # YDTS23Y21-35ZNV001
HERM RECP



TE Part # YDTS21Y21-35SNV001
HERM RECP



TE Part # YDTS23N21-35DNV001
HERM RECP



TE Part # YDTS23H21-35DNV001
HERM RECP



TE Part # YDTS21N21-35ZNV001
HERM RECP



TE Part # YDTS23N21-35SNV001
HERM RECP



TE Part # YDTS24N21-35DNV001
HERM RECP



TE Part # YDTS24N21-35ZNV001
HERM RECP




TE Part # YDTS23H21-35ZAV001
HERM RECP




TE Part # YDTS32F21NV0010000
DUST COVER ASSEM




TE Part # YDTS21Y21-35ZNV001
HERM RECP




TE Part # YDTS24N21-35ZAV001
HERM RECP



TE Part # YDTS21H21-35SNV001
HERM RECP



TE Part # YDTS23H21-35SNV001
HERM RECP



TE Part # YDTS23Y21-35DNV001
HERM RECP

Also in the Series | [DEUTSCH 38999 Series III](#)



[Standard Circular Connectors\(497\)](#)

Also in the Series | [DEUTSCH 38999](#)



[Standard Circular Connectors\(497\)](#)


Customers Also Bought



TE Part # ZPF00000000097856
DBAS 79-61-0 PN 090-1A SCC




TE Part # YDTS24F13-98SAV001
RECP ASSY



TE Part # D8178E61-0PN-1A
PLUG ASSY



TE Part # ZPF00000000097855
DBAS 79-61-0 PY 090-1A SCC



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_YDTS26F21-35PNV001_99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS26F21-35PNV001_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS26F21-35PNV001_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH DTS Series Connectors for 38999 QRG](#)

English