

Part Number: **5690109999F**

General Description	
Series	569
Configuration	3 mm Lens
Description	3 mm Dual Bi -Level CBI B -B-B-B
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Peak Wave Length	428
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Untinted, Diffused
Viewing Angle	70
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Â°)	
Reverse Current	100 @ Vr = 5V
Derating	0.44 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics	
Color	Blue
LED Type	High Efficiency
Peak Wave Length	428
LED Position	1-4
Luminous Intensity Min	7.1
Luminous Intensity Typical	12.5
Forward Voltage Typical	3.5
Forward Voltage Max	4.1
Test Current mA	20mA
Power Dissipation Max	90mW



**5690109999F**

[check stock](#)



This is a [RoHS Compliant Product](#).  
[To learn more click here](#)