

## 404807005001 Product Details

[Share](#) | [Print](#) | [Email](#)


**404807005001**  
(1625938-1)

TE Internal Number: 1625938-1

**Active**

### Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K  $\Omega$
- Resistance = 10K  $\Omega$
- Power Rating = 1.00 W

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Spindle Operated Potentiometers - Type PC908 Series ...](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Potentiometer
- [Element](#) = Cermet
- [Series](#) = PC908
- [Sealed](#) = No
- [Mount Angle](#) = Vertical
- [Termination Type](#) = PCB Terminations

#### Electrical Characteristics:

- Resistance Selection ( $\Omega$ ) = K
- [Resistance \( \$\Omega\$ \)](#) = 10K
- [Power Rating \(W\)](#) = 1.00
- [Tolerance \(%\)](#) = 20

#### Termination Features:

- [Termination Post Orientation](#) = 5.0 x 5.0

#### Body Features:

- [Package, Component Size](#) = 18

#### Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Top
- [Adjustment Style](#) = Edge Control
- [Operating Function](#) = Single Turn

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Other:

- Brand = Citec

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

