


404806411010 Product Details

[Share](#) | [Print](#) | [Email](#)



404806411010
(1-1623849-0)

TE Internal Number: 1-1623849-0

Active

[View 3D PDF](#)

Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = K Ω
- Resistance = 10K Ω
- Power Rating = .50 W

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [PROFESSIONAL TRIMMERS SERIES 4290W](#) (PDF, English)

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Professional Trimmers - Type 4290 Series - Tyco Elec...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version BA)
- [3D Model](#) (IGES, Version BA)
- [3D Model](#) (STEP, Version BA)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Trimmer
- [Element](#) = Cermet
- [Series](#) = 4290
- [Sealed](#) = Yes
- [Mount Angle](#) = Horizontal
- [Termination Type](#) = PCB Terminations

Electrical Characteristics:

- Resistance Selection (Ω) = K
- [Resistance \(\$\Omega\$ \)](#) = 10K
- [Power Rating \(W\)](#) = 0.50
- [Tolerance \(%\)](#) = 10

Termination Features:

- [Termination Post Orientation](#) = In Line

Body Features:

- [Package, Component Size](#) = 10

Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Top
- [Adjustment Style](#) = Screwdriver Slot
- [Operating Function](#) = Multi Turn

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = 100

Other:

- Brand = Citec

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

