



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5219201F	5 mm Lens Single Color
Description	Discrete LED Lamp
Package Options	100 pieces per bag
Product Type	Through Hole Indicators
Sub Product Type	Discrete LED
Configuration	5 mm Lens
Lamp Type	Single Color
Lens Color	Tinted Non-Diff
Viewing Angle	30 degrees
Test Current (mA)	20mA

Absolute Maximum Ratings (Ta = 25 °)	
Reverse Current	100 @ Vr = 5V
Forward Current Continuous	30 mA
Forward Current Pulse	120 mA
Derating	from 50Â° @ .4mA/Â°C
Reverse Voltage	5 V
Solder Temp	260Â° for 5 sec
Operating Temp	-55~+100° C
Storage Temp	-55~+100° C
Peak Wave Length	565

Distributor Stock Check

Check stock with our distributors now.

5219201F

[check stock](#)

how to purchase

- [sales contacts](#)
- [stock check](#)


search

[Product Line Search](#)

Please select a Product Line to search.

Circuit Board Indicators

[find](#)



Operating Characteristics

LED Position
Color
Lamp Type
LED Type
Intensity Min (mcd)
Intensity Typ (mcd)
Intensity Max (mcd)
Fwd Voltage Min
Fwd Voltage Typ
Fwd Voltage Max
Dom Wavelength Min (nm)
Dom Wavelength Typ (nm)
Dom Wavelength Max (nm)
Power Dissipation Max (mW)
Backlighting
Pitch Between Vertical
Pitch Between Horizontal
Lum Intensity Min
Lum Intensity Typ
Lum Intensity Max

Part # / Text Search

Part No.:

Text Search:

[search](#)

[quick links](#)

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes

[FAQs](#)

Dialight Ltd (UK)

[Dialight Garufo](#)

[Dialight BLP](#)

[LumiDrives](#)