



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5219458F	5 mm Lens
Description	Discrete LED Lamp
Package Options	100 pieces per bag
Product Type	Through Hole Indicators
Sub Product Type	Discrete LED
Configuration	5 mm Lens
Viewing Angle	65 degrees
Absolute Maximum Ratings (T _a = 25 °)	
Solder Temp	260Å° for 5 sec
Operating Temp	-20~+100° C
Storage Temp	-55~+100° C


Distributor Stock Check

Check stock with our distributors now.

5219458F

[check stock](#)

- [how to purchase](#)
- [sales contacts](#)
- [stock check](#)



search

[Product Line Search](#)

Please select a Product Line to search.

[find](#)

[Part # / Text Search](#)

Part No.:

Text Search:

[search](#)

[quick links](#)

Operating Characteristics

LED Position	
Color	Red / Green
Lamp Type	Bi-Color / Bi-Color
LED Type	
Intensity Min (mcd)	2.1 / 1.2
Intensity Typ (mcd)	5.0 / 8.0
Intensity Max (mcd)	7.9 / 11.8
Fwd Voltage Min	
Fwd Voltage Typ	1.9 / 2.2
Fwd Voltage Max	2.6 / 3.0
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	626 / 570
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes

[FAQs](#)

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives