

- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5219480F	5 mm Lens Single Color
Description	Discrete LED Lamp
Package Options	100 pieces per bag
Product Type	Through Hole Indicators
Sub Product Type	Discrete LED
Configuration	5 mm Lens
Lamp Type	Single Color
Lens Color	Tinted Diffused
Viewing Angle	60 degrees
Test Current (mA)	5V

Absolute Maximum Ratings (Ta = 25 °)	
Reverse Voltage	5 V
Solder Temp	245Å° for 5 sec
Operating Temp	-40~+100° C
Storage Temp	-55~+100° C
Peak Wave Length	635

Distributor Stock Check

Check stock with our distributors now.

5219480F

[check stock](#)

how to purchase

- [sales contacts](#)
- [stock check](#)

search

[Product Line Search](#)

Please select a Product Line to search.

[find](#)


Part # / Text Search

Part No.:

Text Search:

[search](#)

[quick links](#)



Operating Characteristics	
LED Position	
Color	Red
Lamp Type	Single Color
LED Type	GaAsP/GaP
Intensity Min (mcd)	2.1
Intensity Typ (mcd)	
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	10.0
Fwd Voltage Max	15.0
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	626
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

[Application Notes](#)

[FAQs](#)

[Dialight Ltd \(UK\)](#)

[Dialight Garufo](#)

[Dialight BLP](#)

[LumiDrives](#)