

# Specifications

Photo is representative

## Eaton LSR-S11-1-I-TKG

Eaton LS-Titan Safety Interlock Switch, Cabinet Door Hinge Switches, Polyamide PA66-GF25 enclosure, 6A max AC, 3A max DC, 2NC, Slow Make Break, Positive Opening, 6A at 230Vac, 0.5A at 250Vdc, Screw Terminals

### General specifications

<b>PRODUCT NAME</b>	Eaton LS-Titan Key interlock safety switches
<b>CATALOG NUMBER</b>	LSR-S11-1-I-TKG
<b>UPC</b>	786685393834
<b>PRODUCT LENGTH/DEPTH</b>	1.18 in
<b>PRODUCT HEIGHT</b>	5.98 in
<b>PRODUCT WIDTH</b>	1.26 in
<b>PRODUCT WEIGHT</b>	0.2063 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	LS-Titan
<b>CONTACT RATING</b>	6A at 230Vac, 0.5A at 250Vdc
<b>ENCLOSURE MATERIAL</b>	Polyamide PA66-GF25
<b>CONNECTION</b>	Screw terminal
<b>CONTACT CONFIGURATION</b>	2 NC, slow make break, positive opening
<b>SWITCH TYPE</b>	Cabinet door hinge switch
<b>OPERATING TEMPERATURE - MAX</b>	158 °F
<b>OPERATING TEMPERATURE - MIN</b>	-13 °F
<b>ENVIRONMENTAL RATING</b>	IP66, IP67
<b>MAXIMUM AC CURRENT</b>	6 A
<b>MAXIMUM DC CURRENT</b>	3 A

## Resources

<b>CATALOGS</b>	<a href="#">Sensing Solutions, Limit Switches, Volume 8, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - LSR-S11-1-I-TKG</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

