

- Product Navigation
- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  sales contacts
-  stock check

 search

Product Line Search

Please select a Product Line to search.

Part # / Text Search

Part No.:

Text Search:

 quick links

Dialight Corporate Video


Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators		
P/N# 5530131310F	3 mm Lens	
Description	3 mm Bi-Level CBI	
Package Options	50 Pieces Per Bag	
Product Type	Through Hole Indicators	
Sub Product Type	with Bi-Level Housing	
Configuration	3 mm Lens	
Viewing	Right Angle	
Viewing Angle	45	
Test Current (mA)	10mA	

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-25 to +85° C
Storage Temp	-30 to +100° C



Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Yellow	Red
Lamp Type	Single Color	Single Color
LED Type	Standard Efficiency	Standard Efficiency
Intensity Min (mcd)	2.2	3.6
Intensity Typ (mcd)	6.3	10.0
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	60	60
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.