

Technical specification :


Rated voltage: IEC 61076-2-104	30 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Moulding body:	TPU, UL 94, grey


Contact assignment:

1)	brown	■
2)	white	■
3)	blue	■
4)	black	■
5)	grey	■



Part no:	Description:	Length L:	Cable:
42-11136	SAL - 8B - RKS5.1 - RSS5.1 - 0,3 / A1	0,3m	PVC, grey, 5x0,25mm ² Cable: 781-A1250G
42-11137	SAL - 8B - RKS5.1 - RSS5.1 - 0,6 / A1	0,6m	
42-11138	SAL - 8B - RKS5.1 - RSS5.1 - 1,5 / A1	1,5m	
42-11139	SAL - 8B - RKS5.1 - RSS5.1 - 3 / A1	3m	
42-xxxxx	SAL - 8B - RKS5.1 - RSS5.1 - ... / A1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index:a 23.08.11 BCB Ä3941 data modified	 dim. in mm		title: Connecting cable ø8, female connector axial - male connector axial, snap, B-coding
		date	name	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	drawn 03.09.10	Fromm	dwg no:
		appd. 03.09.10	Mankopf	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			42K1A250
			part no:	see table