



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

### Circuit Board Indicators - Through Hole Indicators

P/N# <b>5680121322F</b>	Rectangle Lens
Description	2X4 mm Quad-Level CBI R-Y-G-G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	Rectangle Lens
Viewing	Right Angle
Viewing Angle	104
Test Current (mA)	10mA

### Absolute Maximum Ratings (Ta = 25 °)

Solder Temp	<b>260Å° for 5 sec</b>
Operating Temp	<b>-55 to +100° C</b>
Storage Temp	<b>-55 to +100° C</b>

**Distributor Stock Check**

Check stock with our distributors now.

5680121322F

[check stock](#)



### Operating Characteristics

	Found in position(s): 1	Found in position(s): 2	Found in position(s): 3,4
LED Position			
Color	Red	Yellow	Green
Lamp Type	Single Color	Single Color	Single Color
LED Type	High Efficiency	High Efficiency	High Efficiency
Intensity Min (mcd)	1.1	0.0	0.0
Intensity Typ (mcd)	3.7		
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)	588	588	588
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)	100	60	100
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			

- how to purchase
- sales contacts
  - stock check

search

Product Line Search

Please select a Product Line to search.

Part # / Text Search

Part No.:

Text Search:

quick links

**Dialight Corporate Video**

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

**Application Notes**

[FAQs](#)

- [Dialight Ltd \(UK\)](#)
- [Dialight Garufo](#)
- [Dialight BLP](#)
- [LumiDrives](#)