



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

| Circuit Board Indicators - Through Hole Indicators | |
|--|-----------------------------|
| P/N# 5682231310F | 3 mm Lens |
| Description | 3 mm Quad-Level CBI R-Y-R-X |
| Package Options | 5 Pieces Per Bag |
| Product Type | Through Hole Indicators |
| Sub Product Type | with Quad Level Housing |
| Configuration | 3 mm Lens |
| Viewing | Right Angle |
| Viewing Angle | 45 |
| Test Current (mA) | 10mA |

Absolute Maximum Ratings (Ta = 25 °)

- [how to purchase](#)
- [sales contacts](#)
- [stock check](#)



Distributor Stock Check

Check stock with our distributors now.

5682231310F

[check stock](#)

search

[Product Line Search](#)

Please select a Product Line to search.

[find](#)

[Part # / Text Search](#)

Part No.:

Text Search:

[search](#)

Operating Characteristics

| LED Position | Found in position(s): 1,3 | Found in position(s): 2 | Found in position(s): 4 |
|----------------------------|---------------------------|-------------------------|-------------------------|
| Color | Red | Yellow | Blank |
| Lamp Type | Single Color | Single Color | Single Color |
| LED Type | High Efficiency | High Efficiency | |
| Intensity Min (mcd) | 8.7 | 10.0 | |
| Intensity Typ (mcd) | 29.0 | | |
| Intensity Max (mcd) | | 50 | |
| Fwd Voltage Min | | | |
| Fwd Voltage Typ | | | |
| Fwd Voltage Max | | | |
| Dom Wavelength Min (nm) | | | |
| Dom Wavelength Typ (nm) | | | |
| Dom Wavelength Max (nm) | | | |
| Power Dissipation Max (mW) | 100 | 60 | |
| Backlighting | | | |
| Pitch Between Vertical | | | |
| Pitch Between Horizontal | | | |
| Lum Intensity Min | | | |
| Lum Intensity Typ | | | |
| Lum Intensity Max | | | |

- [quick links](#)
- [Dialight Corporate Video](#)
- [Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. \[View PDF File\]\(#\)](#)
- [Application Notes](#)
- [FAQs](#)
- [Dialight Ltd \(UK\)](#)
- [Dialight Garufo](#)
- [Dialight BLP](#)
- [LumiDrives](#)