



Circuit Board Indicators	Circuit Board Indicators - Through Hole Indicators	
Panel Mount Indicators		
Solid State Lighting	P/N# 5682232110F	3 mm Lens
Traffic Signals	Description	3 mm Quad-Level CBI G-R-R-X
Vehicle Lighting	Package Options	5 Pieces Per Bag
Rail	Product Type	Through Hole Indicators
Obstruction Lighting	Sub Product Type	with Quad Level Housing
Hazardous Area Lighting	Configuration	3 mm Lens
Heliport Lighting	Viewing	Right Angle
	Viewing Angle	45
	Test Current (mA)	10mA
	Absolute Maximum Ratings (Ta = 25 °)	

how to purchase

 sales contacts

 stock check

 search

 Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

☐ Part # / Text Search

Part No.:

Text Search:


search

 quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives


Distributor Stock Check

Check stock with our distributors now.

5682232110F

[check stock](#)

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2,3	Found in position(s): 4
Color	Green	Red	Blank
Lamp Type	Single Color	Single Color	Single Color
LED Type	High Efficiency	High Efficiency	
Intensity Min (mcd)	32.0	8.7	
Intensity Typ (mcd)	50.0	29.0	
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)			
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)	100	100	
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			