

Dialight - Leader in LED Technology



- ? [Circuit Board Indicators](#)
- ? [Panel Mount Indicators](#)
- ? [Solid State Lighting](#)
- ? [Traffic Signals](#)
- ? [Vehicle Lighting](#)
- ? [Rail](#)
- ? [Obstruction Lighting](#)
- ? [Hazardous Area Lighting](#)
- ? [Heliport Lighting](#)

Circuit Board Indicators - Surface Mount Indicators	
P/N#	PLCC-2 Single Color
5973323302F	
Description	

Region:

Product Line:

Forward Current Continuous	30 mA
Forward Current Pulse	100 mA
Derating	from 40° @ .42mA/°C
Solder Temp	240° for 20 sec
Operating Temp	-55~+100° C
Storage Temp	-55~+100° C
Peak Wave Length	523

Distributor Stock Check

Check stock with our distributors now.



RoHS Compliant Product


Check stock with our distributors now.

Please note that the stock check **is only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.

Please select a Product Line to search.

Part No.:

Text Search:



Operating Characteristics	
LED Position	
Color	Green
Lamp Type	Single Color
LED Type	InGaN
Intensity Min (mcd)	180
Intensity Typ (mcd)	224.0
Intensity Max (mcd)	
Fwd Voltage Min	3.7
Fwd Voltage Typ	4.3
Fwd Voltage Max	
Dom Wavelength Min (nm)	525
Dom Wavelength Typ (nm)	114
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Copyright 2006 Dialight. All rights reserved | [Privacy Policy](#)

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)