



D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	4pos 30 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: DIN 40050-9	IP 69K, in mated condition
Temperature range: IEC 60664-1	-30°C ... +85°C (temporary till +105°C)
Mating cycles: IEC 60512-9a	≥ 100


Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	Thermoplastic GF, UL 94
Sealing:	FPM
Coupling nut:	1.4404 stainless steel
Moulding body:	Thermoplastic elastomere, translucent

Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:



Part no:	Description:	Length L:	Cable:
43-11636	SAL - FB - 12 - RKW4 - 3L - 2 / P1	2m	PP, orange, 4x0,34mm ² Cable: 781-P13400
43-11637	SAL - FB - 12 - RKW4 - 3L - 3 / P1	3m	
43-11638	SAL - FB - 12 - RKW4 - 3L - 5 / P1	5m	
43-11639	SAL - FB - 12 - RKW4 - 3L - 10 / P1	10m	
43-xxxxx	SAL - FB - 12 - RKW4 - 3L - ... / P1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 24.02.11 VF Ä3909 technical specification changed, part no. cable in table added, data sheet modified		 dim. in mm		title: Female connector M12x1 angled, FB with LED	
			date	name		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn	19.02.08	Franz	dwg no: 43K1A619
			appd.	19.02.08	Mankopf	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						
		part no:			see table	