


Material und Oberfläche:
Material and plating:


Gehäuse / housing: LCP, UL94V-0, natural
Kontakt / contact: Kupferlegierung 2.5µm verzinkt, 1.25µm Ni rundum
Copper alloy
2.5µm tin plating over 1.25µm Ni all over

Masse und Toleranzen in Übereinstimmung mit ANSI Y15.5M-1994 /
Interpret dimensions according to ANSI Y15.5M-1994



Layout:

vorgeschlagene Toleranz für PCB Layout ± 0.05
recommended PCB layout tolerance ± 0.05



Verpackung Stange / packaging tube

8	27
6	33
5	37
4	42
3	49
2	58
Polzahl No. of positions	Stück / pieces

109939	8	17.3	22.5	14
109938	6	13.3	18.5	10
109937	5	11.3	16.5	8
109936	4	9.3	14.5	6
109935	3	7.3	12.5	4
109934	2	5.3	10.5	2
Ident.-Nr. part-no. tube	Polzahl	Mass A	Mass B	Mass C

Information:	Tolerances	 All Dimensions in mm	Scale	5:1
	All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Designation iBridge male 2mm pitch Single Row Vertical DIP	
Subject to modification without prior notice. Drawing will not be updated.		 www.ERNI.com	109933	
Index	Date		Class	IBRIDGE

Copyright by ERNI GmbH. Proprietary notice pursuant to ISO 9006 to be observed.

I
A3