

Übergabesteckzone  
mating transfer zone

Elastische Einpresszone mit Übergabesteckzone /  
compliant pressfit zone with mating transfer zone

Isolierwerkstoff / housing material : PBT GF30

Bauart 7 / type 7

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Masse und Angaben gemäß IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions according to IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6

diameter of drilled hole see drawing 164062/No.6

1)  $\phi 1,0 \pm 0,09$  Durchmesser des metallisierten Loches


$\phi 1,0 \pm 0,09$  Diameter of finished plated-through hole

$\phi 1,15 \pm 0,025$  Bohrungsdurchmesser des Loches


$\phi 1,15 \pm 0,025$  Diameter of drilled hole

Bestückungsplan / contact layout

■ bestückt / assemble



Leiterplatten-Lochbild / PCB drillhole pattern



Consider protection memo from DIN 34

Information:  All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Tolerances All Dimensions in mm	Scale 2:1
	Subject to modification without prior notice. Drawing will not be updated.	Designation Federleiste CD 128 EE Fem. Connector CD 128 Pressfit
www.ERNI.com	284181	I
Index	Date	N:00062253.SZA STVCD