

TD228-1203P=TDFO 120 SEC M83726/28-1203P




CII

TE Part # **TD228-1203P**
TE Internal #: **4-1617808-9**

Type of Control : **Fixed**
Input Voltage (VDC): **28**
Contact Current Rating (A): **10A@28VDC, 115VAC**
Mode of Operation : **Delay on Operate**
Delay Time : **120 seconds**

[Similar Products](#)

[Compatible Parts & Tooling](#)



We are here to help!
Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

[Documents](#)

[Features](#)

[Product Compliance](#)

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features Product Category : **Electromechanical Relays**
Relay Type : **Time Delay**
Product Type : **Relay**
Enclosure Type : **Hermetic Sealed Metallic**

Configuration Features Multiple Timing Ranges : **Without**

Electrical Characteristics Input Voltage (VDC): **28**
Actuating System : **DC**

Contact Features Type of Control : **Fixed**
Contact Current Rating (A): **10A@28VDC, 115VAC**
Delay Time : **120 seconds**
Contact Arrangement : **2 Form C, DPDT, 2 C/O**

Termination Features Termination Type : **Solder Pin Terminal**



Mechanical Attachment	Mounting Type : Raised Vertical Flange Mount
Dimensions	Dimensions (L x W x H) (Approximate) : 25.79 x 25.79 x 25.4 mm [1.015 x 1.015 x 1 in]
Usage Conditions	Operating Temperature Range (°C): -55 – 125
Operation/Application	Mode of Operation : Delay on Operate
Other	Repeatability (Max) : ±10%
Statement of Compliance	Statement of Compliance pdf

Need help? ×

Our team is on stand-by and ready to help with your order.

CHAT NOW
>

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)