




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

Connector System: **Board-to-Board**

Number of Positions: **5**

Number of Rows: **1**

Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	5
Number of Loaded Positions	5
Connector Contact Load Condition	Fully Loaded
Number of Positions	5
Number of Rows	1
PCB Mount Orientation	Vertical



Electrical Characteristics

Insulation Resistance	100 MΩ
-----------------------	--------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	4 – 6 μm[157.48 – 236.22 μin]
Contact Shape & Form	Rectangular
Contact Layout	Inline
Contact Mating Area Length	3.5 mm[.138 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	9 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Mating Retention Type	Latch
Mounting Alignment Feature Length	.75 mm[.029 in]
PCB Mount Alignment Type	Locating Posts
Mating Alignment Type	Polarization Groove
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	Without

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	PPA

Dimensions

Connector Width	7 mm[.275 in]
Connector Height	7.8 mm[.307 in]



Connector Length	10.58 mm[.416 in]
------------------	-------------------

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	DIN, UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 504385-E
MCBP 4 M * SMD 137 * 197 * GU-H * J 2 50



TE Part # 544621-E
MCBP 5 F 2 022 137 * 197 1,27 TRAY VR2



TE Part # 514496-E
MCBA 14 M * SMD 137 * 176 * GURT C7 J 2



TE Part # 504425-E
MCBP 6 M * SMD 137 * 197 * GU-H * J 2 50




TE Part # 524431-E
MCBP 5 F 2 035 137 * 197 1,27 TRAY VR2 J



TE Part # 504445-E
MCBP 8 M * SMD 137 * 197 * GU-H * J 2 50




TE Part # 504958-E
MCBA 5 F * 035 137 * 197 1,27 TRAY VR2 J




TE Part # 504345-E
MCBP 2 M * SMD 137 * 197 * GU-H * J 2 50

Also in the Series | ERNI MicroBridge



Board-to-Board Headers & Receptacles(13)




PCB Headers & Receptacles(23)




Rectangular Power Connectors(43)



Standard Rectangular Connectors(20)



Wire-to-Board Connector Assemblies & Housings(2)



Wire-to-Board Headers & Receptacles (2)

Customers Also Bought





TE Part #504285-E
MCBA 8 M * SMD 137 * 176 * GURT * J 2 50



TE Part #504265-E
MCBA 5 M * SMD 137 * 176 * GURT * J 2 50



TE Part #504305-E
MCBA 12 M * SMD 137 * 176 * GURT * J 2 5



TE Part #504345-E
MCBP 2 M * SMD 137 * 197 * GU-H * J 2 50




TE Part #925075
4W CIRCULAR MATE-N-LOK PIN HSG NAT



TE Part #2-964302-1
TAB A 2.8x0.8 CONTACT CF SWS Sn



TE Part #1-967570-1
2POS MQS TAB SEALED COD A



TE Part #1394353-2
FLACHSTE A-P 1,5



TE Part #CAT-N10-RC4828
48V Ready 2.8mm Sealed Connectors

Documents

Product Drawings

MCBP 5 M * SMD 137 * 197 * GU-H * J 2 50

German

CAD Files

Customer View Model

ENG_CVM_CVM_504405-E_1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_504405-E_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_504405-E_1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Datasheet - ERNI MicroBridge Automotive Applications

English

Product Specifications

108-161172 MicroBridge IDC SMT

English

Qualification Results MicroBridge SMT IDC

English