




Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts

 TE Part # 474274-E SRCBUG A 2,54 2-WH 8 CSI 112 E1 ADV J 2	 TE Part # 335104-E SRCBUG A 2,54 2 2 CSI 112 * K-AD B500 J	 TE Part # 384453-E SRCBUG A 2,54 2 4 CSI 112 E1 ADV J 2 324	 TE Part # 374335-E DRCBUG B 2,54 20 * CSI 112 E012 ADV J 2
 TE Part # 364198-E SRCBUG A 2,54 2 2 CSI 112 E1 ADV TRAY J	 TE Part # 474034-E DRCBUG B 2,54 10 * CSI 112 E012 ADV J 2	 TE Part # 515223-E SRCBUG A 2,54 2-KS 10 CSI 112 E1 ADV TRA	 TE Part # 364240-E SRCBUG A 2,54 2 6 CSI 112 E1 ADV J 2 324

Customers Also Bought

 TE Part #364240-E SRCBUG A 2,54 2 6 CSI 112 E1 ADV J 2 324	 TE Part #464743-E SRCBUG A 2,54 2-KS 8 CSI 163 E1 ADV J 2	 TE Part #374335-E DRCBUG B 2,54 20 * CSI 112 E012 ADV J 2	 TE Part #1-456406-5 CRIMPER WIRE .090 F
 TE Part #1333204-1 ANVIL, COMBINATION .080	 TE Part #3-1633965-7 INSULATION CRIMPER	 TE Part #2-1703930-2 NANOMQS, RECEPTACLE TERMINAL	 TE Part #2119784-4 CRIMPER, INSUL O PREMIUM
 TE Part #2312114-1 14POS,NANOMQS,REC HSG ASSY, COD A	TE Part #ET1106-000 RW-200-3/16-0-SP-CS9376		



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_544471-E_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_544471-E_D.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_544471-E_D.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Application Specification

English

Application Specification

English

Application Specification

English