




EMI & EMC Solutions > IEC Inlets > Power Entry Modules > CORCOM P SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**

Input Voltage Selection: **Single AC**

Filter Switch Type: **DPST**

Filter Shield Type: **None**

Product Orientation: **Vertical**

[All CORCOM P Series Multi-Function Inlet Fil \(311\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Unfiltered
Filter Connector Type	IEC 320/C-14

Configuration Features

Fuse Options	Single
--------------	--------

Electrical Characteristics

Input Voltage Selection	Single AC
Current Rating	10 A
Operating Voltage	250 VAC



Body Features

Filter Shield Type	None
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Mounting Ears (Vertical)
--------------------------	--------------------------

Dimensions

Panel Thickness (Recommended)	.13 – 1 mm
-------------------------------	------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C[14 – 104 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998



TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999



TE Part # 1609140-1
PA100=F6800




TE Part # 1609140-3
PA105 J0=F6806

Also in the Series

Corcom P



EMI & EMC Accessories(4)



Medical Power Entry Modules(1)



Power Entry Modules(367)

Customers Also Bought



TE Part #1-480303-0
03P CMNL PLUG HSG F/H NATL

Documents

Product Drawings

PM0S0SBX0=C5288

English

CAD Files

Customer View Model

ENG_CVM_7-6609959-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_7-6609959-4_A.3d_stp.zip

English

Customer View Model

ENG_CVM_7-6609959-4_A.2d_dxf.zip

English

3D PDF

7-6609959-4

Power Entry Module, Single AC Input, DPST, None, Vertical, 10 A, .187" FASTON
Output, 250 VAC, Unfiltered, IEC 320/C-14, Corcom P, Power Entry Modules



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_7-6609959-4_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-6609959-4_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-6609959-4_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English