

4-6609952-3 Product Details



4-6609952-3

EMI/RFI Filters and Accessories

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Filter - EMI/RFI
- Filter Type = Power Entry (Filtered/Unfiltered)
- P (3-10 Amp) Series
- Medical Application
- Mount Style = Snap-in

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

TE Internal Number: 4-6609952-3

 [Active](#)

 [View 3D PDF](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Customer Drawing P-Series](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insertion Loss/Specifications](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Filter - EMI/RFI
- [Filter Type](#) = Power Entry (Filtered/Unfiltered)
- [Filtered](#) = Yes
- [Type of Connector](#) = IEC 320/C-14

Mechanical Attachment:

- [Shield Style](#) = Complete Shield

Electrical Characteristics:

- [Input Voltage Select](#) = Single AC Voltage
- [Current Rating \(A\)](#) = 6
- [Voltage Selection](#) = Single
- [Voltage ≤ \(VAC\)](#) = 250
- Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (µA) = 2
- Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (µA) = 5

Termination Related Features:

- [Terminal Input - Output Combination](#) = IEC - .187" Faston

Body Related Features:

- [Series](#) = P (3-10 Amp)
- [Mount Style](#) = Snap-in
- Switch Type = No Switch

Configuration Related Features:

- Extender Options = None
- [Fuse Options](#) = Dual
- [Fuse Holder Type](#) = Selectable

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = UL Recognized, CSA Certified, VDE Approved

Conditions for Usage:

- Need Min Size With IEC Connector = Yes
- Need Optional Switch, Fusing, Or Voltage Selector = Yes

Operation/Application:

- [Application](#) = Medical

Other:

- Brand = Corcom
- Facility Installation = No

 BOOKMARK  

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat with Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

