



2-1609109-1 Product Details

Share Print Email



2-1609109-1
(PM0S0DL6C)

TE Internal Number: 2-1609109-1

Active

View 3D PDF

EMI/RFI Filters and Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Filter - EMI/RFI
- Filter Type = Power Entry (Filtered/Unfiltered)
- P (3-10 Amp) Series
- High Performance Medical Application, Switching Power Supply Application
- Mount Style = Mounting Ears (Vertical)

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- [CUSTOMER DRAWING PM0S0DL6C](#) (PDF, English)

Catalog Pages/Data Sheets:

- [1-1654250-1 CORCOM EMI RFI QRG](#) (PDF, English)
- [5-1773450-6 CORCOM HIGH PERFORMANCE P SERIES WITH VE...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insertion Loss/Specifications](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Filter - EMI/RFI
- [Filter Type](#) = Power Entry (Filtered/Unfiltered)
- [Series](#) = P (3-10 Amp)
- [Filtered](#) = Yes
- [Type of Connector](#) = IEC 320/C-14

Mechanical Attachment:

- Shield Style = Complete can

Electrical Characteristics:

- [Input Voltage Select](#) = Single AC Voltage
- [Current Rating \(A\)](#) = 6
- [Voltage Selection](#) = Single
- [Voltage ≤ \(VAC\)](#) = 250
- Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (µA) = 2
- Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (µA) = 5

Termination Features:

- [Terminal Input - Output Combination](#) = IEC - 1/4" Faston

Body Features:

- [Mount Style](#) = Mounting Ears (Vertical)
- [Switch Type](#) = DPST

Configuration Features:

- Extender Options = None
- [Fuse Options](#) = Dual
- [Fuse Holder Type](#) = Selectable

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = UL Recognized, VDE Approved, CSA Certified

Operation/Application:

- [Application](#) = High Performance Medical, Switching Power Supply

Other:

- Brand = Corcom
- Comment = Fits 1U high enclosure.

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Search Knowledge Base
Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

