

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register \(Why Register?\)](#)

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types



- [Aerospace & Defense](#)
- [Appliance](#)
- [Automotive](#)
- [Communications](#)
- [Computer & Consumer Electronics](#)
- [Industrial & Commercial](#)
- [Instrumentation & Medical Equipment](#)

[By Brand](#)

[A to Z](#)

[Documentation](#)

[Find](#)

- [Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

[Resources](#)

[RoHS](#)

- [Compliance & Alternates](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

[My Account](#)

[Sign In](#)

[Register](#)

[Customer Support](#)

[Support](#)

- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [eBulletin Newsletter](#)

[Home](#) > [Products](#) > [By Type](#) > [PolySwitch Resettable Devices](#) > [Product Feature Selector](#) > Product Details

MINISMDC125F/16-2 Product Details



MINISMDC125F/16-2

Raychem Part Number: D23571-000

 [Active](#)

PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Family Name = miniSMD
- Surface Mount Construction
- IH (Room Temperature) = 1.25 Amps.
- IT (Room Temperature) = 2.50 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [miniSMDC125F/16](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)**Product Type Features:**

- UL Recognized = 20040119-E74889

Electrical Characteristics:

- [IH \(Room Temperature\) \(Amps.\)](#) = 1.25
- [IT \(Room Temperature\) \(Amps.\)](#) = 2.50
- [Vmax Operating \(V\)](#) = 16
- [Rmin \(\)](#) = 0.05
- [R1 Max \[Post Trip\] \(\)](#) = 0.14
- [UL Rated Current \(Amps.\)](#) = 100
- Tripped Power Dissipation (Typical) (W) = 0.80

Termination Related Features:

- Construction = Surface Mount

Body Related Features:

- CSA File No. = 1031175 (CA 78165-1)

Contact Related Features:

- Family Name = miniSMD

Configuration Related Features:

- [Form Factor \(inches\)](#) = 1812
- [Form Factor \(mm\)](#) = 4532

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041438

Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Related Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© [2007 Tyco Electronics Corporation All Rights Reserved](#)