

DTS26F23-35PN [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Series III, DEUTSCH 38999

TE Internal #: YDTS26F23-35PNV001

100 Position Circular Connector, Cable-to-Panel, Sealable, Wire & Cable, Signal, Panel Mount, Electroless Nickel, Aluminum 6061-T6, N Code

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug: D38999, 23-35 Insert, Electroless Nickel Plating



Connector System: **Cable-to-Panel**

Connector Mounting Type: **Panel Mount**

Number of Positions: **100**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

[All Straight Plug: D38999, 23-35 Insert, Electroless Nickel Plating \(2\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Number of Positions	100
Number of Power Positions	0
Number of Signal Positions	100
Contacts Preloaded	No

Body Features

Shell Plating Material	Electroless Nickel
Shell Base Material	Aluminum 6061-T6
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No



Contact Features

Contact Current Rating (Max)	5 A
Reverse Gender	No
Contact Layout Arrangement	23 – 35
Circular Connector Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	23
Alignment Keyed	Clocking

Dimensions

Wire Size	28 – 22 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
Shielded	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.2% in Contact Lead-Copper Alloy) Decamethylcyclpentasiloxane (D5) (5% in Insert subassembly)

Article Safe Usage Statements:



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # YDTS24N23-35ZNV001
HERM RECP



TE Part # YDTS23N23-35SNV001
HERM RECP



TE Part # YDTS23H23-35ZNV001
HERM RECP



TE Part # YDTS24Y23-35DNV001
HERM RECP



TE Part # YDTS24Y23-35SNV001
HERM RECP



TE Part # YDTS23Y23-35ZAV001
HERM RECP



TE Part # YDTS23H23-35DNV001
HERM RECP



TE Part # YDTS20Y23-35SNV001
HERM RECP



TE Part # YDTS21Y23-35ZAV001
HERM RECP






TE Part # YDTS23N23-35DNV001
HERM RECP




TE Part # YDTS24N23-35ZAV001
HERM RECP




TE Part # YDTS23N23-35ZAV001
HERM RECP



Also in the Series | **DEUTSCH 38999 Series III**



Also in the Series | **DEUTSCH 38999**




Customers Also Bought




TE Part #YDTS24F23-35SNV001
RECP ASSY



TE Part #0479490001
HTCM-SCE-1/2-4H-9



TE Part #089827-000
B-040-26-N



TE Part #CAT-T3437-T548
TMS-SCE Military Grade Sleeves



TE Part #34133
SPLICE,PG PARA 16-14



TE Part #34135
SPLICE,PG PARA 12-10



TE Part #YDTS26F11-35PBV001
PLUG ASSY



TE Part #YDTS26F25-35SAV001
PLUG ASSY



TE Part #YDTS26T15-35PEV001
PLUG ASSY

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_YDTS26F23-35PNV001_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS26F23-35PNV001_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS26F23-35PNV001_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH DTS Series Connectors for 38999 QRG](#)

English